


B152000N2

SERIES _____
 B15= FORM C
 POLES _____
 2= 2 POLE & 3= 3 POLE
 CURVED BASE DIAMETER _____
 000= FLAT BOTTOM
 MATERIAL AND HOUSING COLOUR _____
 N= PA6 BLACK
 SCREW AND GASKET _____
 2= NBR FLAT GASKET & SCREWS






NOTES
 1. PLEASE SEE TABLE FOR CURRENTLY CONFIGURED PART NUMBERS.
 FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT
 THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED.
 2. FOR PACKAGING SEE PACKAGING SPEC PPK-121012-B15
 3. PRODUCT SPEC: SEE PS-12101-001
 4. TERMINALS BENT AFTER INSERTION FOR BEND ANGLE SEE TABLE
 5. 2P+T BASE SHOWN IN DRAWING

LAST INSPECTION NUMBER 5

PART No.	mPm PART No.	DESCRIPTION	TERMINAL BEND ANGLE (°)
1210120009	B152000N2	TYPE C 2P BLACK, NBR FLAT GASKET & SCREWS	45
1210120010	B153000N2	TYPE C 3P BLACK, NBR FLAT GASKET & SCREWS	45



ITEM	DESCRIPTION
1	SCREWS
2	TERMINALS
3	HOUSING
4	INSERT
5	GASKET



ORIGINAL RELEASE EC NO: IPG2013-1132 2013/01/28 DRWN:DSHEA CHKD:SMGREVY 2013/01/29 APPR:STGRIFFIN 2013/02/08	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY DSHEA	DATE 2013/01/28	TITLE B15 SERIES BASES			
			4 PLACES	± ---	± ---	CHECKED BY	DATE				
			3 PLACES	± ---	± ---	APPROVED BY STGRIFFIN		DATE 2013/02/08	MOLEX MOLEX INCORPORATED		
			2 PLACES	± 0.10	± ---						
			1 PLACE	± 0.20	± ---	SEE CHART		SD-121012-009		1 OF 1	
ANGULAR ± 2 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					