


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs. / 100 pcs. (g)	RECOMMENDED TOOL SETTING
	MIN. in (mm)	MAX. in (mm)											
PLT1M	.06 (1.5)	.87 (22)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	3.9 (99)	11 (49)	MINIATURE	CURVED	.06 (27)	GS2B MIN 2
PLT1.5I	.06 (1.5)	1.38 (35)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	5.6 (142)	18 (80)	INTERMEDIATE	CURVED	.10 (46)	GS2B INT 3
PLT2S	.06 (1.5)	1.88 (48)	.052 (1.3)	.190 (4.8)	.258 (6.6)	.220 (5.6)	.316 (8.0)	7.4 (188)	30 (133)	STANDARD	CURVED	.23 (104)	GS2B STD 5
PLT3S	.06 (1.5)	3.00 (76)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	11.5 (292)	30 (133)	STANDARD	CURVED	.35 (139)	GS2B STD 5
PLT4S	.06 (1.5)	4.00 (102)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	14.5 (368)	30 (133)	STANDARD	CURVED	.43 (195)	GS2B STD 5
PLT2H	.188 (4.8)	2.00 (51)	.075 (1.9)	.300 (7.6)	.320 (8.1)	.290 (7.4)	.480 (12.2)	8.1 (206)	50 (222)	HEAVY	STRAIGHT	.61 (277)	GS4H HVY 5
PLT3H	.188 (4.8)	3.00 (76)	.075 (1.9)	.300 (7.6)	.320 (8.1)	.290 (7.4)	.480 (12.2)	11.4 (290)	50 (222)	HEAVY	STRAIGHT	.79 (359)	GS4H HVY 5
PLT4H	.188 (4.8)	4.00 (102)	.075 (1.9)	.300 (7.6)	.320 (8.1)	.290 (7.4)	.480 (12.2)	14.5 (368)	50 (222)	HEAVY	STRAIGHT	1.0 (454)	GS4H HVY 5

NOTES:

- * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 2) MATERIAL SUFFIX CODE: -100=WEATHER RESISTANT BLACK
-109=PANDUIT STANDARD POLYPROPYLENE
IS OFF-SHADE GREEN

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS			
										SS-15356-10.PRT			
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										PAN-TY CABLE TIES PLT SERIES			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1(2.5) (.XXX) ± .010(.25) (.XX) ± .20(.5) ANGLES ± -----		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY CEW	MAT'L: POLYPROPYLENE		SCALE NONE
10	9/9/04	ERW	CORRECTED METRIC CONVERSIONS				15356	10		DATE 1-22-85			DWG A
REV	DATE	BY	CHK	DESCRIPTION				ECN - R	CUST	SUP	CHK'D HVP	SS-15356	