

PRODUCT DATASHEET

Pro 3 LED Headlight **Energizer**

HD33A1EN

HANDS-FREE

- Light where you need it without having to hold it
- Swivel and tilt adjustment aims light



VERSATILE

- Operates in 2 modes – flood and night vision
- Multiple position slide switch



ECONOMICAL

- Runs 28 ½ hours on one set of batteries in white flood mode
- LEDs never need replacing



BRIGHT

- Provides 30 lumens of light in white flood mode
- Uses premium Nichia® LED technology.



Lightweight, versatile and comfortable, the Energizer® Pro 3 LED Headlight is perfect for work that requires both hands. It puts light where you are looking with its swivel and tilt adjustment.

Variable light sources allow you to choose the best illumination for the job – white flood or night-vision red. Also, this light mounts securely and can be comfortably worn around the head for long periods of time.



Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:


Designation:	Energizer Pro 3 LED Headlight	
Model:	HD33A1EN	
Color:	Green	
Power Source:	Three "AAA"	
ANSI/NEDA:	Series 24	
Lamp:	Two White LEDs, One Red LED	
Lamp Life (hr):	Lifetime	
Mode:	White	Red
Lamp Output (lumens):	30	2
Run Time (h:mm):	28:30	58:30
Beam Distance (m):	23	N/A*
Peak Beam Intensity (cd):	132	N/A*

* Beam Distance and Peak Beam Intensity are not applicable to colored LEDs

Typical Weight: 77 grams with batteries

Dimensions (mm): 45 x 67 x 40

Performance:



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
 ©Energizer / All Rights Reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Energizer:](#)

[HD33A1EN](#)