




Wiha Vinyl Grip Pliers & Cutters

Wiha Pliers & Cutters, professional quality at competitive prices. A wide selection covering most applications in which pliers & cutters are required.

Precision formed

Jaws & Cutters
induction
hardened



Heavy duty steel
riveted joints

Vinyl grips are
oil & solvent
resistant

High frequency induction
hardened body from C.V.
tool steel forgings



Combination Pliers


[SHOP](#)

326 Combination Pliers DIN ISO 5746

Extra long cutting edge for flat and round cables. Serrated jaws. Cutting edges additionally induction hardened to approx. 60HRC. C.V. Special tool steel. For gripping and holding as well as cutting soft and hard wires and cables. Soft vinyl grips, oil & solvent resistant.

Item No.		mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
326 03	Z01016001	160	6.3	#10	1	.41
326 06	Z01018001	180	7.0	#9	1	.50
326 09	Z01020001	200	8.0	#8	1	.63

High Leverage Combination Pliers



With Lower Serrated Pulling Jaws

[SHOP](#)

326 High Leverage Heavy Duty Combination Pliers DIN ISO 5746

Extra long cutting edge for flat and round cables. Serrated upper jaws and lower pulling jaws. Cutting edges additionally induction hardened to approx. 60HRC. C.V. Special tool steel forgings. Use For gripping, pulling & holding as well as cutting soft, hard & piano wires and cables. Soft vinyl grips are oil & solvent resistant.

Item No.		mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
326 12	Z02020001	200	8.0	#4	1	.61
326 15	Z02022501	225	9.0	#4	1	.78

Stripping Pliers


[SHOP](#)

326 45 Stripping Pliers DIN ISO 5744

Heavy duty forged with induction hardened cutting edges for even stripping of insulation. Easy to use adjusting screw allows the stripping diameter to be set. Opening spring for effortless and sensitive handling of pliers. C.V. special tool steel. For Stripping up to Ø 5mm/#4 AWG conductor cross-section. Soft vinyl grips.

Item No.		mm	Inch	Stripping Capacity Copper Awg#	Pkg.	wt.
326 45	Z55016001	160	6.3	#4 - #28	1	.31