

form: A3

APPLICATION SPECIFIC					
PIN	STYLE	MATING	SOLDER	"C"	"J"
03		5.84	2.41	1.52	12.44
04		5.84	3.05	1.52	12.44
06		10.72	13.39	1.52	17.32
07		12.32	13.39	1.52	18.92
08		3.05	3.05	1.52	9.65
09		6.04	1.6	1.52	12.64
10		10.89	3.05	1.52	17.49
14		5.82	7.8	1.4	12.3
15		3.2	10	1.52	9.8
18		3.5	6.4	1.4	10
20		13	3.23	1.52	19.6
22		7.48	1.6	1.52	14.08

mat'l. code				surface	tolerance		projection	product family	
				ISO 1302	ISO 406	ISO 1101		BSTIK	
ltr	ecn no	dr	date	tolerances unless otherwise specified				title	
AA	F00135	DLE	00.02.23	angles	linear		mm	HEADER,DR,RA,	
AB	F00145	LMU	00.03.07					2.54 mm	
AC	F00461	LMU	00.07.11				scale		
AD	F20116	DLE	02.01.17	dr	G LEOTY	95.08.26		dwg no	sheet 2 of - size
AE	F03-0203	LMU	03.04.28	engr	COMPAGNON J	95.08.26		76350	A3
AF	F05-0186	LMU	05.06.09	chr				type CUSTOMER Drawing	
AG	F06-0207	LMU	06.07.27	appd	JMC	95.08.26			
sheet index	revision sheet								