







## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0=±0.4  
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 6A @125V, 3A @250VAC
5. CONTACT RESISTANCE: 50m ohm Max. (INITIAL)
6. INSULATION RESISTANCE: DC 500V 100M ohm Min.
7. DIELECTRIC STRENGTH: AC 1500V 1 minute.
8. ▲ DENOTES CRITICAL PARAMETER.



RECOMMEND PANEL MOUNTING  
6MM PANEL THICKNESS MAX.



| ▲ SWITCH FUNCTION |        |
|-------------------|--------|
| POS. 1            | POS. 2 |
| OFF               | ON     |
| OPEN              | 2-1    |

|      |         |                         |          |      |
|------|---------|-------------------------|----------|------|
| C    | 14511   | REMOVE HARDWARE NOTE    | 11/16/04 | AR   |
| B    | 13109   | UPDATE NOTES            | 5/7/03   | AR   |
| A    | 10262   | RELEASED FOR PRODUCTION |          |      |
| REV. | ECN No. | DESCRIPTION             | DATE     | CHKD |

THE INFORMATION CONTAINED IN THIS DOCUMENT  
IS PROPRIETARY TO E-SWITCH AND IS  
NOT TO BE COPIED OR TRANSFERRED

**E-SWITCH®**

TITLE

RR3402A 05

SCALE

1.5:1

DATE

7/2/99

DR

MM

DWG

F030003

REV

C