

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192210223

Status:

Active

Description:


Compression Style Ring Tongue Terminal for 8 AWG Wire, Stud Size 10, Plated,

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Ring and Spade Terminals
Series	19221
Comments	Heavy Duty
Mil-Spec	N/A
Product Name	Battery Cable Lug
Type	Ring
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min: Mating (µin)	160
Plating min: Mating (µm)	4
Plating min: Termination (µin)	160
Plating min: Termination (µm)	4
Stud Size	10 (M5)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size AWG	8
Wire Size mm²	6.60 - 10.5
Electrical	
CSA	LR18689
UL	E32244
Material Info	
Old Part Number	BCL-810-PL
Reference - Drawing Numbers	
Sales Drawing	SD-19221-001



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19221Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Putt Pump Dieless Head System	0192860065
Hand Crimp Tool	0192840034
Die Set (large) for the HHLS Hydraulic Crimper	0192900001
Manual Putt Pump Hydraulic System, Die set required	0192860117
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	0192940008

This document was generated on 02/03/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION