

Home - Distributor Area - Distributors - Support - Jobs - Contact

Choose your language: English (US)

Search Product:

CAMSETW13U

Submit

[[Advanced](#)]



- [Adapters & power supplies](#)
- [Batteries & chargers](#)
- [Cables & accessories](#)
- [Connectors](#)
- [Consumer products & pc acc.](#)
- [Electronic components](#)
- [High-q tools & dmm's](#)
- [Lamps & led's](#)
- [Led products & lamps](#)
- [Light products](#)
- [Loudspeakers & pa systems](#)
- [Perel tools](#)
- [Security products](#)
- [Velleman kits & oscilloscopes](#)



[ROHS Info](#)

[SECURITY PRODUCTS](#) > [WIRELESS A/V TRANSMISSION](#) >



WIRELESS CAMERA WITH USB RECEIVER - 2.4GHz

Order Code: CAMSETW13U



Features

- built-in microphone
- IR LEDs
- 3 main functions: instant viewing, alarm function, night vision
- recording function, image capture, task planning
- baby monitoring function: recording with a detection of a sound or PIR (programmable per channel)
- image viewing via notebook, PC or TV

Specifications

- camera:
 - sensor: CMOS
 - resolution: 510 X 492
 - viewing angle: 55°
 - min. illumination: 5 lux (F1.2, IR off)
 - transmission frequency: ISM 2400MHz - 2483MHz
 - transmission power: 10mW
 - modulation type: FM
 - bandwidth: 18MHz
 - power supply: 8VDC / 300mA (adapter incl.) or 3 x 1.5V AAA batteries ([LR03C](#), not incl.)
 - motion detection distance: 8m
 - motion detection area: 120° (horizontal), 15-25° (vertical)
 - sound sensitivity: > 50dB
 - power consumption: 180mA (IR off), 230mA (IR on)
 - transmission range: max. 260 ft in open field
 - night vision range: 16 ft
 - dimensions: 3 11/32" x 4 19/64" x 4 3/8"

- weight: 6 oz
 - 4 channels selectable: 2414, 2432, 2450, 2468MHz
- receiver:
 - receiving frequency: ISM 2400 - 2483MHz
 - intermediate frequency: 480MHz
 - demodulation type: FM
 - sensitivity: < -85dBm
 - transmission interface: USB 2.0
 - dimensions: 4 9/64" x 55/64" x 2 23/32"
 - weight: 3 oz
- system requirements:
 - CPU: 2.0GHz or higher
 - memory: 256MB RAM
 - USB 2.0 port
 - HDD: 30GB or more
 - CD-ROM drive
 - colour monitor or LCD display
 - audio/video card supporting DirectX 9.0 or later
 - Windows® XP
- recording:
 - compression: MPEG4
 - file format: AVI
 - image size: 720 x 576, 352 x 576, 352 x 288
 - frame rate: 5, 10, 15, 20, 25 fps

Files

- [EN - FR - NL - ES - DE](#)

Stock Info

- Inner carton:
- Outer Carton:
- EAN Barcode:
- UPC Barcode: 836479008489
- Packaging:

(C) 2005 Velleman Components N.V.
[[Disclaimer](#)]