
**KEMET Part Number: MR/C-01** 



## KEMET, ZCT, Current, Round - Toroidal, Zero Phase, High Sensitivity, Compact



Dimensions		
D	6mm MIN	
Н	6.7mm MAX	
D2	17.5mm MAX	
D3	19mm MAX	

Packaging Specifications		
Packaging:	Tray	
Packaging Quantity:	1200	
Weight:	2.3 g	

General Information	
Series:	ZCT
Туре:	Current
Style:	Round - Toroidal
Description:	Zero-Phase Current Transformers
Features:	High Sensitivity, Compact
Lead:	2 Pin
RoHS:	Yes
Notes:	Measurement Conditions: f=60Hz, R=300 Ohms, lo=22.5 mAmps

Specifications		
Temperature Range:	-20/+80C	
Voltage DC:	12.5 mV MIN (Output)	
Current:	15 Amps	
Resistance:	30 Ohms	
Miscellaneous:	Overinput characteristics (After DC5A input) = 10% MAX	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

