

# 3M™ Mini D Ribbon (MDR) Cable Assembly

.050" High Speed Digital Data Transmission System, 100 Pos. 141A0-SZ5B-XXX-0DC



- 24 shielded quad pairs (96 cond.) plus 4 drains
- Solution for high speed datacom and telecom applications
- Each differential pair is shielded with foil and braid for additional signal protection
- Rugged MDR ribbon type contact
- Quick release latches
- RoHS\* compliant

Date Modified: October 11, 2005

TS-0966-05  
Sheet 1 of 3

---

## Physical

### Connector Contact Plating

Wiping Area: 30  $\mu$ " [ 0.76  $\mu$ m ] Min. Gold

### Shell

Plating: Nickel

Material: Aluminum

### Cable

Color: Parchment/Beige

Jacket Material: Polyvinyl Chloride (PVC)

Flammability: AWM VW-1

---

## Electrical

**Voltage Rating:** 30 V

**Insulation Resistance:**  $> 1 \times 10^8 \Omega$  at 100 Vdc

**Withstanding Voltage:** 350 Vrms for 1 minute

**Current Rating:** 1 A

### Individually Shielded Balanced Quads

**Characteristic Impedance:**  $100 \pm 10 \Omega$

**Conductor Size:** 30 AWG

**Propagation Velocity:** 1.45 ns/ft [4.8 ns/m ]

---

## Environmental

**Temperature Rating:** -20°C to +75°C

"RoHS compliant" means that the product or part does not contain any of the following substances in excess of the following maximum concentration values in any homogeneous material, unless the substance is in an application that is exempt under RoHS: (a) 0.1% (by weight) for lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers; or (b) 0.01% (by weight) for cadmium. Unless otherwise stated by 3M in writing, this information represents 3M's knowledge and belief based upon information provided by third party suppliers to 3M.

UL File No.: E86982



Interconnect Solutions



<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.  
For technical, sales or ordering information call

800-225-5373

# 3M™ Mini D Ribbon (MDR) Cable Assembly

.050" High Speed Digital Data Transmission System, 100 Pos. 141A0-SZ5B-XXX-0DC



MDR 100 Position Plug  
Both Ends

mm  
[Inch]

| Tolerance Unless Noted |     |      |
|------------------------|-----|------|
|                        | 0.0 | 0.00 |
| mm                     | ±.1 | ±.10 |

[ ] Dimensions for  
Reference only



## Ordering Information

**141A0-SZ5B-XXX-0DC**

Length: \_\_\_\_\_  
300 = 3 meters  
500 = 5 meters

TS-0966-05  
Sheet 2 of 3



Interconnect Solutions

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.  
For technical, sales or ordering information call

**800-225-5373**

# 3M™ Mini D Ribbon (MDR) Cable Assembly

.050" High Speed Digital Data Transmission System, 100 Pos. 141A0-SZ5B-XXX-0DC

| MDR 100 Position Pinout F100-1 |             |       |      |             |       |
|--------------------------------|-------------|-------|------|-------------|-------|
| Quad                           | Signal      | Pin # | Quad | Signal      | Pin # |
|                                | LVDS GRND 1 | 1     | 2    | 25M         | 26    |
| 11                             | 1M          | 51    | 2    | 26M         | 76    |
| 11                             | 2M          | 2     | 2    | 25P         | 27    |
| 11                             | 1P          | 52    | 2    | 26P         | 77    |
| 11                             | 2P          | 3     | 7    | 27M         | 28    |
| 12                             | 3M          | 53    | 7    | 28M         | 78    |
| 12                             | 4M          | 4     | 7    | 27P         | 29    |
| 12                             | 3P          | 54    | 7    | 28P         | 79    |
| 12                             | 4P          | 5     | 8    | 29M         | 30    |
| 13                             | 5M          | 55    | 8    | 30M         | 80    |
| 13                             | 6M          | 6     | 8    | 29P         | 31    |
| 13                             | 5P          | 56    | 8    | 30P         | 81    |
| 13                             | 6P          | 7     |      | LVDS GRND 3 | 32    |
| 14                             | 7M          | 57    | 9    | 31M         | 82    |
| 14                             | 8M          | 8     | 9    | 32M         | 33    |
| 14                             | 7P          | 58    | 9    | 31P         | 83    |
| 14                             | 8P          | 9     | 9    | 32P         | 34    |
| 15                             | 9M          | 59    | 10   | 33M         | 84    |
| 15                             | 10M         | 10    | 10   | 34M         | 35    |
| 15                             | 9P          | 60    | 10   | 33P         | 85    |
| 15                             | 10P         | 11    | 10   | 34P         | 36    |
| 16                             | 11M         | 61    | 18   | 35M         | 86    |
| 16                             | 12M         | 12    | 18   | 36M         | 37    |
| 16                             | 11P         | 62    | 18   | 35P         | 87    |
| 16                             | 12P         | 13    | 18   | 36P         | 38    |
| 17                             | 13M         | 63    | 19   | 37M         | 88    |
| 17                             | 14M         | 14    | 19   | 38M         | 39    |
| 17                             | 13P         | 64    | 19   | 37P         | 89    |
| 17                             | 14P         | 15    | 19   | 38P         | 40    |
|                                | LVDS GRND 2 | 65    | 20   | 39M         | 90    |
| 3                              | 15M         | 16    | 20   | 40M         | 41    |
| 3                              | 16M         | 66    | 20   | 39P         | 91    |
| 3                              | 15P         | 17    | 20   | 40P         | 42    |
| 3                              | 16P         | 67    | 21   | 41M         | 92    |
| 4                              | 17M         | 18    | 21   | 42M         | 43    |
| 4                              | 18M         | 68    | 21   | 41P         | 93    |
| 4                              | 17P         | 19    | 21   | 42P         | 44    |
| 4                              | 18P         | 69    | 22   | 43M         | 94    |
| 5                              | 19M         | 20    | 22   | 44M         | 45    |
| 5                              | 20M         | 70    | 22   | 43P         | 95    |
| 5                              | 19P         | 21    | 22   | 44P         | 46    |
| 5                              | 20P         | 71    | 23   | 45M         | 96    |
| 6                              | 21M         | 22    | 23   | 46M         | 47    |
| 6                              | 22M         | 72    | 23   | 45P         | 97    |
| 6                              | 21P         | 23    | 23   | 46P         | 48    |
| 6                              | 22P         | 73    | 24   | 47M         | 98    |
| 1                              | 23M         | 24    | 24   | 48M         | 49    |
| 1                              | 24M         | 74    | 24   | 47P         | 99    |
| 1                              | 23P         | 25    | 24   | 48P         | 50    |
| 1                              | 24P         | 75    |      | LVDS GRND 4 | 100   |

TS-0966-05  
Sheet 3 of 3



Interconnect Solutions

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.

For technical, sales or ordering information call

**800-225-5373**

## Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



### Electronics

6801 River Place Blvd.  
Austin, TX 78726-9000  
800/328-1368  
[www.3M.com/electronics](http://www.3M.com/electronics)

## Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Minimum 10%  
Post-Consumer Fiber

Printed in USA.

© 3M 2005