


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 5016164185
Status: Active
Overview: FFC-FPC (SMT)
Description: 0.30mm Pitch Easy-On Type FPC Connector, 1.10mm Mated Height, Right Angle, Surface Mount, ZIF, Top Contact Style, 41 Circuits



Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-501616-003-001 \(PDF\)](#)
[Packaging Specification SPK-501616-001-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	FFC/FPC Connectors
Series	501616
Overview	FFC-FPC (SMT)
Product Name	Easy-On
UPC	822350923361
Physical	
Circuits (Loaded)	41
Color - Resin	Black, Gray
Contact Position	Top
Durability (mating cycles max)	10
Entry Angle	90° Angle
Mated Height	1.10mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	112.034/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.30mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount
Wire/Cable Type	FPC only

Electrical	
Current - Maximum per Contact	0.2A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers	
Packaging Specification	SPK-501616-001-001
Product Specification	PS-501616-003-001
Sales Drawing	SD-501616-007, SD-501616-008

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

501616 Series