

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300940255

Status:

Active

Overview:

Support Grips

Description:

Standard Duty Support Grip, Offset Eye, Closed Mesh, Single Weave, Cable Diameter 19.05-25.15mm (.750-.990"), Approximate Break Strength 435.45kg (960 lbs)

Documents:

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

CSA

LR32159

General

Product Family

Series

Exclude SD Check

Eye Type

O-Ring

Overview

Product Literature Order No

Product Name

Type

UPC

Cable Grips

130094

Yes

Offset

N/A

Support Grips

987650-8065

Standard Duty

Support Grip

78678835062

Physical

Approximate Break Strength

Bale Length

Body Style

Cable Diameter

Color - Grommet

Gender

Material - Body

Material - Grip

Mesh Length

Number of Holes

Thread Size

435.45kg (960 lbs)

0.102m (4.00")

Straight

19.05-25.15mm (.750-.990")

N/A

N/A

N/A

Non-magnetic Tin Bronze Wire

0.356m (14.00")

N/A

N/A

Material Info

Engineering Number

35062



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130094 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION