



Quartz Crystal

MHz range

SMD-version

model	KX - 20	
frequency range	3,579545 ~ 25,0 MHz	
mode	fundamental, 3 rd overtone	
operating temperature	standard -20° ~ + 70°C available -40° ~ + 85°C (= KX-20T) available -40° ~ +105°C (= KX-20E)	
frequency tolerance at +25°C	± 50 ppm	
temperature tolerance	at -20° ~ + 70°C ± 50 ppm at -40° ~ + 85°C ± 100 ppm at -40° ~ +105°C ± 120 ppm	
load capacitance C_L	standard 16 pF available 12 ~ 20 pF	
series resonance R_1 max.	fundamental 3,5 ~ 3,9 MHz 150 Ohm 4,0 ~ 5,99 MHz 120 Ohm 6,0 ~ 7,99 MHz 80 Ohm 8,0 ~ 9,99 MHz 60 Ohm 10,0 ~ 45,0 MHz 50 Ohm 3 rd overtone 32,0 ~ 70,0 MHz 100 Ohm	
aging (first year)	± 5 ppm	
shunt capacitance C_0 max.	7,0 pF	
drive level in mW	0,1	
contents of reel	2000 pcs.	
RoHS	since production start	
part no.	12.87500~12.87799	

