






X
(without protection hood)

Loading-Plan

Y
(without protection hood)



A — blue — B
B — orange — A



For Information Only
won't be replaced when changed

-Protection level: IP67/65
-Temperature range: -40°C ...+70°C

11	High strength fiber optic breakout cable Single Mode	33 58 211 300 0002	300 m
10	High strength fiber optic breakout cable Single Mode	33 58 211 100 0002	100 m
9	High strength fiber optic breakout cable Single Mode	33 58 211 060 0002	60 m
8	High strength fiber optic breakout cable Single Mode	33 58 211 050 0002	50 m
7	High strength fiber optic breakout cable Single Mode	33 58 211 040 0002	40 m
6	High strength fiber optic breakout cable Single Mode	33 58 211 030 0002	30 m
5	High strength fiber optic breakout cable Single Mode	33 58 211 020 0002	20 m
4	High strength fiber optic breakout cable Single Mode	33 58 211 010 0002	10 m
3	High strength fiber optic breakout cable Single Mode	33 58 211 005 0002	5 m
2	High strength fiber optic breakout cable Single Mode	33 58 211 003 0002	3 m
1	High strength fiber optic breakout cable Single Mode	33 58 211 001 0002	1 m
Cont No.	Type of cable	Part-No.	Dim. a

All Dimensions in mm Original Size DIN A 3				Techn. Character.			Nicht tolerierte Maß/Free size tolerances	
DRS1044A	02.02.12	RO		Dat.	Name	Maßstab/Scale	PushPull fiber optic assembly 2xPushPull LC DUPLEX, plastic Single Mode	
DRS532B	04.09.09	RA	Detail.	20.08.08	MR	2:1		
DRS506A	21.05.09	MS	Insp.	20.08.08	RA			
EC00166	17.02.09	MR	Stand.					
35590	13.01.09	MR	HARTING Electronics GmbH & Co. KG			HARTING	TB 33 58 211 xxx 0002	
35014			D-32339 ESPELKAMP					
Mod.	Dat.	Name					Sub.	Sub.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33582110010002](#) [33582110050002](#) [33582110100002](#) [33582110200002](#) [33582110400002](#) [33582110500002](#)
[33582111000002](#)