



A771 Carbon Monoxide Adapter for DMMs and Clamp-on Meters

What about Carbon Monoxide?

National Ambient Air Quality Primary Standards in the US call for less than 9 ppm carbon monoxide for an 8 hour average during any 12 month period.

Concentrations of 1 to 2 ppm may be found in homes with a normally operating gas furnace to well over 1,000 ppm in homes with a faulty furnace.

Just 200 ppm CO over 2 to 3 hours can cause slight headache, fatigue, dizziness, and nausea.

Carbon Monoxide testing is a crucial service provided by HVAC/R technicians.

Turn over for technical information and accessory part numbers.

The Value Leader™



Measure Ambient Air CO With Any DMM

- No Bulk! Easily carry one on your belt or tool box
- Easy to use with any DMM or Clamp-on Meter with a minimum 3 1/2 digit LCD, 2 or 4 Volt DC range and 10M or greater input impedance
- A771 generates 1mV per 1ppm of CO
- Detects CO levels from 0-1999 ppm, with resolution as low as 0.1ppm and $\pm 5\%$ of reading accuracy
- Low battery and power indication
- Calibrate in the field
- Complete with Belt pouch, A771P
- Use as personal CO alarm

**3-YEAR
LIMITED
WARRANTY**



Actual size
6.5" X 2.0" X 1.25"
65 X 50 X 29mm

Use Your DMM And The A771 For These Carbon Monoxide Applications

- Conduct Tests of CO Levels In Room Air To Meet ASHRAE and OSHA Standards
- Confirm Proper Operation of Alarming CO Detectors in Households
- Check For Proper Installation of Ventless Gas Fireplaces, Furnaces, and Other Combustion Devices.
- Use The A771 as a Personal Alarm Preset at 30 CO



TECHNICAL SPECIFICATIONS AND ACCESSORIES

- Digital Multimeters
- Clamp Meters
- Hand-held Oscilloscopes
- Refrigerant & Combustible Gas Leak Detectors
- Temperature Testers
- BNC Coax Cable Connectors
- Test Leads
- Accessories

Test Products

International, Inc.

Headquarters:

9615 SW Allen Blvd.

Beaverton, OR 97005

USA

503-520-9197

Fax: 503-520-1225

email:

info@tpi-thevalueleader.com

Test Products

International, Ltd.

342 Bronte St. South

Unit 9

Milton, Ontario L9T

5B7

Canada

905-693-8558

Fax: 905-693-0888

email:

info@tpicanada.com

Test Products

International UK Ltd.

Longley House, East Park

Crawley, West Sussex

RH10 6AP England

Tel: +44 (0)1293 561212

Fax: +44 (0)1293813465

contactus@tpieurope.com

A771 Carbon Monoxide Adapter for DMMs and Clamp-on Meters

SPECIFICATIONS

CO Sensor	24 month warranty
Range	0 - 1999ppm with 3.5 digit DMM display
Alarms	Visual/Audible
Alarm Set Range	0 to 200ppm
Response Time	90% of reading in 30 seconds
Operation Temperature	-10° to 50° or -50° to 122°F
Relative Humidity	5 to 95% RH
Accuracy	±5ppm or 5% of reading whichever is greater
Size	6.5 x 2.1 x 1.2 in (165 x 55 x 30 mm)
Weight	7.23oz (205 g)
Battery	9V Alkaline
Battery Life	500 hours

Distributed By:



To learn about the entire
line of TPI products visit:

www.tpi-thevalueleader.com

L A771-1104

Copyright © 2004 Test Products International, Inc.