

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202350008](#)
Status: **Active**
Overview: [Brad M23 Signal and Power Connectors](#)
Description: Brad M23 Power Connector, Front Panel-Mount Receptacle Housing Only, Straight Male Flange Mount 4xØ 3.20mm

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Field Attachable / Accessories
Series	120235
Application	Power
IP Rating	IP67
Material - Contact	N/A
Overview	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906301880
Physical	
Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	22.000/g
Orientation	Straight
Poles	N/A
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	N/A
Material Info	
Engineering Number	KRP0G06-003
Reference - Drawing Numbers	
Sales Drawing	SD-120235-023



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Low-Halogen	China RoHS
For more information, please visit Contact US	
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Reviewed

Search Parts in this Series
[120235](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION