


OPEN-END WRENCHES

OPEN-END WRENCH 44



Computer-aided design and manufacture


Full CAD/CAM facilities - calculation of all radii, cross-sections and profiles, together with stress analysis for optimum configuration and minimum bulk - were used to perfect this high-performance wrench 44 with slim profile and powerful torque.



Powerful torque

Optimum alloy-steel structure and heat treatment throughout ensure high strength. The long shank of wrench 44 allows extra leverage without compromising safety.

Tightening torque: ISO 1711, DIN 899, NF E 74.381



Slim profile

Streamlined heads improve manoeuvrability and user comfort. Recessed fasteners are easier to reach and rotate, even in confined spaces (30° increments).



High precision

CAM optimizes manufacturing accuracy and repeatability. Tight tolerances on sizes and high-quality finish ensure perfect fit on fasteners and grip in the hand for maximum safety and user comfort.

STANDARD SERIES

▼ 44 METRIC AND INCH OPEN-END WRENCHES

► ISO 10102, DIN 3110, NF E 74-304

- Metric sizes from 3.2 to 42 mm.
- Inch sizes from 1/4" x 5/16" to 1 7/16" x 1 5/8".
- Satin chrome finish.

ISO A x A' mm	ISO A x A' "	B x B' mm	C mm	L mm	ΔΔ g
44.3,2X5,5		11,0 x 13,5	3,0	90	11
44.4X5		11,0 x 13,5	3,0	90	11
44.6X7	44.1/4X5/16	15,5 x 17,5	3,5	120	20
44.8X9		18,5 x 21,0	3,8	137	30
44.8X10	44.11/32X13/32	19,0 x 23,0	4,2	143	38
44.10X11	44.3/8X7/16	23,0 x 25,0	4,7	152	47
44.10X13		23,0 x 29,0	5,1	162	58
44.11X13		25,5 x 29,0	5,1	167	65
44.12X13	44.7/16X1/2	25,5 x 29,0	5,1	167	64
44.12X14	44.1/2X9/16	29,0 x 33,5	5,5	177	77
44.14X15		31,0 x 33,0	5,8	182	87
44.13X17		31,0 x 37,0	6,3	192	118
44.16X17		35,5 x 37,0	6,3	200	118
44.16X18	44.5/8X11/16	37,0 x 42,0	6,8	210	144
44.17X19	44.11/16X3/4	37,0 x 42,0	6,8	210	144
44.18X19		39,0 x 42,0	7,3	220	157
44.20X22	44.3/4X13/16	43,0 x 48,5	7,5	240	200
44.21X23		47,0 x 50,5	7,8	242	218
44.22X24	44.7/8X15/16	47,5 x 52,0	8,3	261	258
44.24X27		51,0 x 58,0	8,8	270	324
44.25X28		56,0 x 61,6	8,8	282	360
44.26X28	44.1"X1"1/16	56,0 x 61,6	8,8	282	360
44.27X29		59,0 x 64,0	9,5	301	450
44.27X30		59,0 x 64,0	9,5	301	450
44.27X32	44.1"1/8X1"1/4	63,0 x 70,0	9,8	318	513
44.30X32	44.1"3/16X1"5/16	63,0 x 70,0	9,8	318	513
44.33X35		71,0 x 75,0	11,5	342	720
44.34X36		71,0 x 75,0	11,5	342	720
44.36X41	44.1"3/8X1"1/2	78,0 x 87,0	12,0	381	945
44.38X42	44.1"7/16X1"5/8	78,0 x 87,0	12,0	381	945

