






LOC		DIST		REVISIONS						
-		-		P	LTR	DESCRIPTION	DATE	DWN	APVD	
					B2	REVISED PER ECO-17-012433	24AUG2017	SK	DD	




SECTION A-A

POKE-IN CAVITIES
ACCEPTS 18 AWG PRE-STRIPPED
SOLID WIRE
STRIP LENGTHS: 9.53±0.8mm
[3/8"±1/32"]


IDC AREA
1811027-1 ACCEPTS 12 AWG SOLID OR STRANDED (19 STRANDS MAX), THHN WIRE
1811027-2 ACCEPTS 18 AWG SOLID TFN/TEWN WIRE
CONTINUOUS (FEEDTHRU) WIRE




SCALE 2:1



SCALE 2:1





SCALE 2:1



SCALE 2:1

1811027-1

1811027-2



TERMINATED DETAIL

△ MATERIAL:
HOUSING: THERMOPLASTIC, COLOR: SEE TABLE
STUFFER: THERMOPLASTIC, COLOR : SEE TABLE
CONTACT: COPPER ALLOY, 0.50 THICK

△ FINISH:
CONTACT: TIN PLATE

3. PRODUCT SPECIFICATION: 108-2219
APPLICATION SPECIFICATION: 114-13151

△ THE LOGO MAY BE JUST "TYCO" UNTIL COMPONENTS
ARE CONVERTED.

GRAY	14 AWG	1811027-3
BLUE	18 AWG	1811027-2
BROWN	12 AWG	1811027-1
CONNECTOR COLOR	FEED THRU WIRE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. FABIAN CHK J. ALLISON APVD 16-Nov-07	28-Oct-04 16-Nov-07 16-Nov-07	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		±" ±" ±0.13 ±0.013 ±" #1		PRODUCT SPEC 108-2219 APPLICATION SPEC 114-13151	
MATERIAL		WEIGHT		SIZE CAGE CODE DRAWING NO A100779C=1811027	
CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1	
				REV B2	