




Fig. 1




Fig. 2




Fig. 3





Fig. 4

- Series 4XX are available with straight and right angle solder tails.
- Series 450 & 499...009 use MM #3404 and #5011/5113 pins. See pages 179 & 181 for details.
- Series 410 & 499...003 use MM #1001 and #1103/1602 receptacles. See pages 136, 137 & 138 for details.
- Receptacles use Hi-Rel, 4 finger #30 BeCu contact rated at 3 amps. See page 218 for details.
- Insulators are high temp. thermoplastic.



Ordering Information

Fig. 1	Series 450...006 Straight Pin Header	
	450-XX-2 _ _ -00-006000	
Specify # of pins	02-64	
Fig. 2	Series 499...009 Right Angle Pin Header	
	499-10-2 _ _ -10-009000	
Specify # of pins	02-64	
For Electrical, Mechanical & Environmental Data, See pg. 4 XX=Plating Code See Below For RoHS compliance select ◇ plating code.		
SPECIFY PLATING CODE XX=		10◇ 90 40◇
Pin Plating		10μ" Au 200μ" Sn/Pb 200μ" Sn
Fig. 3	Series 410...001 Straight Socket	
	410-XX-2 _ _ -41-001000	
Specify # of pins	02-64	
Fig. 4	Series 499...003 Right Angle Socket	
	499-XX-2 _ _ -10-003000	
Specify # of pins	02-64	
For Electrical, Mechanical & Environmental Data, See pg. 4 XX=Plating Code See Below For RoHS compliance select ◇ plating code.		
SPECIFY PLATING CODE XX=		13◇ 43◇
Sleeve (Pin)		10μ" Au 200μ" Sn
Contact (Clip)		30μ" Au 30μ" Au