



30W Interchangeable Plug Series PSAA30R Adapter Series Meets Level VI Efficiency Requirements



Features

- Limited Power Source
- Level VI Efficiency Compliance
- Class II Double Insulated
- Class B EMI

Applications

- Peripherals
- Gaming Machines
- Point of Sale Equipment
- Network Equipment

Safety Approvals

- cUL/UL
- SAA
- CE
- C-Tick

Mechanical Characteristics

- Length: 82.7mm (3.26in)
- Width: 55mm (2.17in)
- Height: 39.1mm (1.54in)
- Weight: 150g (5.29oz)

Output Specifications

Model	DC Output Voltage	Load		Ripple P-P (max.)	Regulation		Efficiency Level
		Min.	Max.		Line	Load	
PSAA30R-120	12V	0A	2.50A	120mV	±5%		VI
PSAA30R-150	15V	0A	2.00A	200mV	±5%		VI
PSAA30R-240	24V	0A	1.25A	240mV	±5%		VI
PSAA30R-560	56V	0A	0.54A	560mV	±5%		VI

(1) Measured with by-pass capacitors 0.1uF/10uF at output connector terminal and oscilloscope set at 20MHz.

(2) At no load to full load, 1.5 meter (approx 5ft) DC cord, measured at the plug

-- Interchangeable clips sold separately

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

