

MICRO SWITCH
FREEPOR T ILLINOIS USA
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-ENCLOSED

**CATALOG LISTING
64CX SERIES
CHART 2**

**64CX SERIES
CHART 2**

M
DRAWING
NUMBER

X
X
X
X
X
X

REVISIONS

A C048504

J A P

21 OCT 80

B C0

53444

WJM

23 JAN 84

C C056479

KEW

4 JAN 85

D C057575

JAS

1 JULY 85

E C058369

KEW

20 NOV 85

F C061401

DAW

16 APR 87

27 M.F.R.

CLE

CHECK

27 M.F.R.

CLE

CHECK

27 M.F.R.


CLE

CHECK

27 M.F.R.

CLE

CHECK



NOTES

- 1 - EXPLOSION PROOF - UNDERWRITERS LAB INC LISTING FOR HAZARDOUS LOCATIONS CLASS I, GROUPS B, C & D; CLASS II, GROUPS E, F AND G
- 2 - ALUMINUM ENCLOSURE FINISHED WITH BLACK EPOXY PAINT
- 3 - 6-32 UNC X 4,75 REF PAN HEAD TERMINAL SCREW (6 PER BASIC)
- 4 - CAMS MAY BE REPOSITIONED IN 7°20' INCREMENTS
- 5 - FOR USE IN TEMPERATURES UP TO 85°C
- 6 - UNIT PROVIDES NO SHAFT RESTORING FORCE, THE ACTUATING DEVICE MUST CONTROL MOVEMENT OF SHAFT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

SCALE 3/4 TO 1
DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE \pm

DIM.	TOL.	DIM.	TOL.
MM	mm/in	IN.	mm/in
XX		XX	
XXX		XXX	
XXXX		XXXX	

SI METRIC

US CUSTOMARY

DESIGN UNITS

RAW MATERIAL-COMMERCIAL STANDARD

MICRO SWITCH STANDARDS APPLY

DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED

WEIGHT 1,25 Kg APPROX

CONVERSION CHART	
0,05	.002
4,75	.187
7,29	.287
8,33	.329
9,4	.37
9,5	.37
12,7	.50
17,8	.70
18,3	.72
20,3	.80
25,4	1.00
29,5 ± 1,5	1.150 ± 0.059
32,0	1.26
40,0	1.57
50,8	2.00
60,35	2.38
80,0	3.15
97,0	3.82
101,6	4.00
133,0	5.24
145,0	5.71
0,5 Nm	.3 PF
1,25 Kg	2.75 LB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[64CX12-D01](#)