



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


|                                                |                                                                                                                                                            |
|------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material                                       | High Conductivity Seamless Copper Tube                                                                                                                     |
| Plating                                        | Electro-Tin                                                                                                                                                |
| Wire Size                                      | 350 STR/FLEX                                                                                                                                               |
| Wire Type                                      | Stranded Copper:<br>Class G, H, I, K, M,<br>Locomotive                                                                                                     |
| Wire Strip Length                              | 2-9/16 in.                                                                                                                                                 |
| Stud Size                                      | 3/8 in.                                                                                                                                                    |
| UL Listed Wire Connector                       | Yes, for applications up to 35kv.<br>Consult cable manufacturer for<br>voltage stress relief instructions<br>with applications greater than<br>2000 volts. |
| UL Temperature Rating                          | 90° C                                                                                                                                                      |
| C.S.A Certified Wire Connector                 | Yes                                                                                                                                                        |
| Panduit Color Code on Barrel                   | BLUE                                                                                                                                                       |
| Panduit Die Index No. on Barrel                | P76                                                                                                                                                        |
| Alternate Industry Die Index No. ( ) on Barrel | (19)                                                                                                                                                       |



LISTED  
Wire Connector



Color coded  
barrel markings



| 00  | 6/03 | SAC | SAC | RELEASED    | 10850 |
|-----|------|-----|-----|-------------|-------|
| REV | DATE | BY  | CHK | DESCRIPTION | ECN   |

**PANDUIT CORP. TINLEY PARK, ILLINOIS**

LCBX350-38H-6  
Copper Lug - One-Hole, Long Flex Barrel, 45° Angle Tongue

SCALE  
N/A

DRAWING NO / CAD FILE

LCBX350-38H-CUST