

Ratings:

Current 8A
Voltage 300 V
Wire Size 28-16AWG
Test Voltage / Dirt Level 4.0 kV/3
Rated Torque / Screw Size 0.4Nm /M2

Rated Cross Section:

Single Wire (solid) 1.5mm²
Stranded Wire (flexible) 1.0mm²
Stranded Wire with Ferrules 1.0mm²

Dimensions:

Spacing 3.81mm
Stripped Length 7.0mm

Materials:

Insulating Material PA
Flammability UL94V-0
Temperature -30°C/+105°C
Block CuZn
Contact CuSn
Color Green

