

AMP


WIRE RANGE

4 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

1. TONGUE MATERIAL THK 1.22±0.08[.048±.003]
FOR 9.70[.382] MAX INS DIA



#10	5.00±0.08 [.197±.003]	-	LOOSE PC	1-331456-0
#8	4.43±0.08 [.171±.003]	-		331456
"B"	"A"	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105° c		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN S.S. GOULDEN 6-21-93		 TE Connectivity											
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: -		DIMENSIONS: MM[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK R. HERSEY 6-21-93		APVD B. BARE 6-21-93			NAME							
	FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 16.8-26.7mm² [33,100-52,600] STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -		TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 4 AWG								
	FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL COPPER PER ASTM B-152 NYLON (MIL-M-20693) TYPE 1 COLOR: YELLOW		FINISH TIN PLATE PER MIL-T-10727		APPLICATION SPEC -		WEIGHT -		SIZE A3		CAGE CODE 00779		DRAWING NO C-331456		RESTRICTED TO -
CUSTOMER DRAWING										SCALE NTS		SHEET 1 of 1		REV D2							