




5

4

3

2

1




SPECIFICATIONS

FREQUENCY (MHz)	ATTENUATION (dB)
5	0,5
10	1
50	2,5
100	3
500	3,5
1000	4

Operating voltage	< 250 V AC
Working current	< 7,5 A
Insulation resistance	> 1GΩ
Contact resistance	< 15 mΩ
Dielectric withstanding voltage	500 V AC / minute

Solder bucket termination inner diameter: 1,20 mm

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, female, straight, 9 poles, tin plated shell, solder buckets, ferrite filter	Maßstab/ Scale 1,5:1
			Detail.	11/06/09	PK			
			Insp.					
			Stand.					
36160	22/09/10	SC	HARTING EURL F-95972 Paris				TB 09 64 111 7800	Blatt/ Page 1 / 1
EC00332	11/06/09	PK						
Mod.	Dat.	Name						
09 64 111 7800		PL3						
Part number		Performance level						