


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NUMBER	BUNDLE DIA.		A	B	C	D	E	F	G	H	J	WRITE-ON AREA	MINIMUM LOOP TENSILE	CROSS-SECTION	WEIGHT (g)
	MIN (in)	MAX (in)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in. (mm)	lbs. (N)		lbs./100 pcs.
BM1M	.18 (4.8)	0.90 (23)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	4.2 (107)	1.12 (28.5)	.31 (7.9)	.03 (.8)	.29 × 1.09 (7.4 × 27.7)	18 (80)	MINIATURE	.09 (40)
BM2M	.18 (4.8)	2.00 (51)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	7.9 (201)	1.12 (28.5)	.31 (7.9)	.03 (.8)		18 (80)	MINIATURE	.15 (69)

NOTES:

*SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS					
										PANDUIT CORP. TINLEY PARK, ILLINOIS					
										DOME-TOP Barb Tie MARKER TIE BM SERIES					
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± --- (.XXX) ± .020 (.5) (.XX) ± .02 (.5) ANGLES ± ---			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
										DRAWN BY JABO		MAT'L: NYLON 6.6		SCALE NONE	
										DATE 5-30-97				DRAWING NO. BT-0248	
										CHK'D JVL				DWG A SIZE	
5	12/1/04	ERW		REWORDED TITLE BLOCK			0248	5							
REV	DATE	BY	CHK	DESCRIPTION			ECN	R	CUST	SUP					