




Product Data Sheet

Part No. PB-2317 Non-Washable Type

PB-2317



DIMENSIONS



$\phi 23.0 \times H17.0$

Type	Unit	PB-2317
Rated Voltage	(VDC)	12
Operating Voltage	(VDC)	3-16
Current Consumption	(mA)	< or = 8
Sound Output (Min)	(dB)	> or = 90
Resonance Frequency	(Hz)	3700 $\pm$ 500
Operating Temp	(C)	-20~+60
Storage Temp	(C)	-30~+70
Weight	(g)	5
Dimension	mm	23 x H17
*Value applying at rated voltage		
*distance for measurement 30cm		