

Honeywell FED.MFG.CODE 91929		SWITCH — BASIC		CATALOG LISTING	
				V7-1C37D8-000-1 CW-B1779	

CATALOG LISTING

V7-1C37D8-000-1

PAGE 1 OF 1

RELEASE NO. PR-23723

REPLACES X110702-V7

PLASTIC PLUNGER

REVISIONS

A	CO-94990	JJA	13 APR 99	
B	0041170	JA	03JUL08	

CHECK

03JUL08

ASD

CHECK

30 OCT 98

JAF

CHECK

30 OCT 98

TSM

30 OCT 98

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF HONEYWELL.

CHARACTERISTICS OPERATING FORCE — — — 150 GRAMS MAX RELEASE FORCE — — — 25 GRAMS MIN DIFFERENTIAL TRAVEL — — — .002—.010 OVERTRAVEL — — — — — .050 MIN FREE POSITION — — — — — .625 MAX RELEASE TRAVEL — — — — — .010 MIN	ELECTRICAL DATA CONTACT ARRANGEMENT S P N C L215 15.1A 1/2HP 125, 250 OR 277 VAC 1/2A 125 VDC 1/4A 250 VDC; 5A 125 VAC "L"	SCALE FULL DO NOT SCALE PRINT UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT
--	---	---

DRAWN

TSM

