





- NOTE:
1. TEST:DC 300V/1s
 2. INSULATION RESISTANCE:10m ohm
 3. CONTACT RESISTANCE::2 ohm
 4. PRODUCTS MEASURE UP TO THE ROHS
 5. PVC TEGUMENT

10	PE BAG 6**9**0.04MM	1PCS
9	ELLIPTICAL CABLE TIE WITH CORE L=70MM	1PCS
8	TIN WIRE LEAD-FREE Ø0.6 ROHS	0.45g
7	P1&P2 PVC , BLACK 45P	16g
6	CONDUCTIVE COPPER PLATINUM P1.W:25MM*L:45MM1PCS ; P2.W:20MM*L:35MM1PCS	2PCS
5	GUMMED PAPER P1.W:20*L:50MM; P2.W:15*L:35MM	2PCS
4	PET&P2 TRANSPARENT PE INTERNAL MODEL MATERIALS,LOW DENSITY	6g
3	HDMI C TYPE MALE: SHORT BODY PIN G/F,IRON SHELL-PLATED NICKEL,INSULATION BLACK	1PCS
2	HDMI A TYPE MALE: SHORT BODY PIN G/F,IRON SHELL-PLATED NICKEL,INSULATION BLACK	1PCS
1	UL20276[30AWG(7/0.10TS)*1P+EA+AL/MY]*4+30AWG(7/0.10TS)*1P+30AWG(7/0.10TS)*5C+AE8(16/6/0.12AM) OD:6.0mm PVC BLACK TEGUMENT CUT L=990±10mm(LS)	1PCS
No	DESCRIPTION	QTY



CnC Tech, LLC

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差參考表		TITLE: HDMI A/M TO CM CABLE PVC	
X.X	±0.38	X.X°	±3.00°
X.XX	±0.25	X.XX°	±2.00°
X.XXX	±0.10	X.XXX°	±1.00°

1	2	3	4	5	6	7	8	9	10
A	B	C	D	E	F	G	A	B	C