


LOC FT	DIST 0	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			M	REVISED PER ECO-08-029122	22NOV08	HMR	MS
			M1	REVISED PER ECO-09-021826	10SEP09	KK	AEG

D

C

B

A



- 1 PARTS PACKAGED UNASSEMBLED.
- 2 CABLE CLAMPING AREA ADJUSTABLE FROM .010 TO .161 SQ IN BY REVERSING CLAMPING INSERTS. (2 INSERTS SUPPLIED).
- 3 CABLE CLAMPING AREA ADJUSTABLE FROM .010 TO .161 SQ IN BY CHANGING CLAMPING INSERTS. (4 INSERTS SUPPLIED, -4 ONLY).
- 4 .453 MAXIMUM CABLE OUTSIDE DIAMETER.
- 5 BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 200 ONLY.
- 6 OBSOLETE PART NUMBER.
- 7 ZINC PLATED NON-HEXAVALENT CHROMATE.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

2 7	5 BULK	$.50 \pm .005$	#5-20	206966-9
8 2 7	7 OBSOLETE SMALL PACK	$.50 \pm .005$	#5-20	206966-8
2 7	INDIVIDUAL	$.50 \pm .005$	#5-20	206966-7
8 7	7 OBSOLETE SMALL PACK	$.50 \pm .005$	#5-20	206966-6
2	AMP BRAZIL USE ONLY INDIVIDUAL	$12\text{mm} \pm .08$	3mm-20	6 206966-5
	INDIVIDUAL	$.50 \pm .005$	#5-20	6 206966-4
7	5 BULK	$.50 \pm .005$	#5-20	206966-2
7	INDIVIDUAL	$.50 \pm .005$	#5-20	206966-1
	PACKAGING	SCREW LENGTH	SCREW TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL THERMOPLASTIC

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN A GRAFF 4/23/91

CHK W.G.LENKER 7-23-92

APVD -

PRODUCT SPEC 108-10024

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation Harrisburg, PA 17105-3608

CABLE CLAMP KIT, STANDARD, SHELL SIZE 13, CPC

SIZE A3

CAGE CODE 00779

DRAWING NO C-206966

RESTRICTED TO -

SCALE NTS

SHEET 1 OF 1

REV M1