

Search within category

GO

VB1B2C3BN30P1



Vertical power strip 60 A, 208V, 24 IEC C-13 and 6 IEC C-19 receptacles, three 20 A double pole magnetic breaker/on-off switch with integral switch guard, red LED current monitor, and 10' power cord with IEC 60309 – 2P+E pin in sleeve water tight connector. UL and c-UL Listed. Dimensions: 66.3"H x 2.0"W x 2.0"D Breaker Doghouse add 1.44" (87.4mm) to overall depth (1683mm x 51mm x 51mm)

This part number has been obsoleted with no replacement. [Click here](#) to contact customer service for further assistance.

- Specs
- Packaging Details
- Documents

OM Obsolete Code	OBSOLETE
CE Compliant	No
UL Listed	Yes
Rack PDU Type	Basic Rack PDU with Local Meter
Monitoring	Local Meter
Remote Outlet Switching	No
Mount Orientation	Vertical
Current Rating (Amps)	60A
Input Voltage	208V - Single Phase
Plug Type	IEC 60309 - 6H 2P+E Blue Watertight
Output Voltage	208V
Receptacle Type	IEC C-13 and IEC C-19
Total Number of Outlets	30
Depth (In.)	2.00
Depth (mm)	50.8
Height (In.)	66.25
Height (mm)	1682.8
Width (In.)	2.00
Width (mm)	50.8
Tool-Less Button Spacing (In.)	64.75
Tool-Less Button Spacing (mm)	1644.7
No. of Rack Spaces	0
Surge Suppression	No
Cable Length	3
RoHS Compliancy Status	Compliant
Min. Order Qty.	1