


Thin Film Type Polyacene Capacitors

PAS2126FR2R5504



■ Features

- Item Summary
2.5V, 0.5F \pm 20%, Less than 0.08 Ω
- Lifecycle Stage
Mass Production

■ Products characteristics table

Temperature Range	-25 to +60°C
Maximum Usable Voltage	2.5V
Nominal Capacity	0.5F
Internal Resistance	0.08 Ω
Initial Capacitance	0.5F \pm 20%
Initial Internal Resistance	Less than 0.08 Ω
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Manual

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
Before making final selection, please check product specification.

2012.09.23