



2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NO.	WEIGHT lbs 10 (g) pcs
JP75CMB-___	.855 (388)



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
- HOOK MATERIAL: NYLON 6/6
ANGLE BRACKET MATERIAL: PRE-GALVANIZED STEEL,
RIVET MATERIAL: ALUMINUM
- PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM OF 3/4" (19.05) DIAMETER BUNDLE. MAXIMUM RECOMMENDED STATIC LOAD: 15 lbs.
- PRODUCT INCORPORATES FEATURES ALLOWING USER TO RETAIN CABLE BUNDLES IN J-PRO J-HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
- PRODUCT MARKINGS:
cULus logo and statement:
"SUITABLE FOR USE IN AIR HANDLING SPACES IN ACCORDANCE WITH SECTION 300-22 (C) & (D) OF THE NATIONAL ELECTRIC CODE."
ULC logo and statement:
"IN ACCORDANCE WITH CAN/ULC S-102.2-10 IN SINGLE UNITS OR PAIRS, 4 ft (1220mm) MIN. SPACING, FSR=0, SDC=35."

TITLE J-PRO CEILING MOUNT J-HOOK (JP75CMB-___)				CONTROL DRAWING	
ITEM REVISION NAME 121031AA/00		PANDUIT TM		MATERIAL: SEE NOTE 2	
DATASET FILE NAME 121031AA_DC_C11000/00A					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x : .1 [2.54] .xxx : .005 [.127] .xx : .01 [.25] ANGLES : 5 °				DRAWING NUMBER: C11000	
		THIRD ANGLE PROJECTION			
DRAWN BY DBLA	DATE 10/29/2012	CHK KLN	SCALE NONE	SIZE A	
SHT 1 OF 1					

OO	10/29/2012	DBLA	GGC	KLN	INITIAL RELEASE	GAECN00219
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

2

1

B

A

A

A

A