



METRIC
DIMENSIONS LISTED IN mm [INCHES]



AMP WIRE RANGE	E13288 Listed
12-10 AWG STRANDED	12-10 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

AMP 12-10* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN - - - - - TOLERANCES ON - - 2 PLG DEC ± - 3 PLG DEC ± - ANGLES ± - MATERIAL	DR 2-8-93 IA BRINKMAN CHK 2-8-93 DA PATTERSON APPD 2-8-93 DE MILLER APPD 2-8-93 JL MECKLEY PRODUCT SPEC	NAME AMP Incorporated Harrisburg, PA 17105-3608
FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	APPLICATION SPEC WEIGHT -	SIZE CAGE CODE 00779 DRAWING NO 31113
TERMINAL, RING TONGUE, BUDGET		

31113
PART NO

31113