

#### Features

- ◆ Ultra wide 4:1 input voltage
- ◆ I/O isolation 5000 VACrms rated for 250 working voltage
- ◆ 2 x MOPP Medical safety according to AAMI/ANSI ES 60601-1:2005(R) and IEC/EN 60601-1 3rd edition
- ◆ Low leakage current <2  $\mu$ A
- ◆ Very high efficiency up to 88%
- ◆ Extended operating temperature range -40°C to 88°C at full load.
- ◆ Input filter to meet EN55022 class A
- ◆ 3-year product warranty



The THM-6WI series is a range of high performance, regulated 6 Watt DC/DC converters in a DIP-24 plastic package. The reinforced I/O-isolation system complies with the medical safety requirements for MOPP (Means Of Patient Protection). Together with a wide 4:1 input voltage range, and an internal EMI filter to meet EN55022 class A the converters constitute also a reliable solution for many demanding applications such as transportation systems, industrial control equipments, measurement equipments, and some IGBT driver applications. With A high efficiency of up to 88% and highest grade components the converters can reliably operate in an ambient temperature range of -40 up to +88°C at full load.

#### Models

| Order code   | Input voltage range                    | Output voltage | Output current max. | Efficiency typ. |
|--------------|----------------------------------------|----------------|---------------------|-----------------|
| THM 6-0510WI | <b>4.5 – 9 VDC</b><br>(5 VDC nominal)  | 3.3 VDC        | 1800 mA             | 81.5 %          |
| THM 6-0511WI |                                        | 5.0 VDC        | 1200 mA             | 86.0 %          |
| THM 6-0512WI |                                        | 12 VDC         | 500 mA              | 86.0 %          |
| THM 6-0513WI |                                        | 15 VDC         | 400 mA              | 86.0 %          |
| THM 6-0515WI |                                        | 24 VDC         | 250 mA              | 87.0 %          |
| THM 6-0521WI |                                        | ±5.0 VDC       | ±600 mA             | 84.0 %          |
| THM 6-0522WI |                                        | ±12 VDC        | ±250 mA             | 86.5 %          |
| THM 6-0523WI |                                        | ±15 VDC        | ±200 mA             | 87.5 %          |
| THM 6-2410WI | <b>9 – 36 VDC</b><br>(12 VDC nominal)  | 3.3 VDC        | 1800 mA             | 83.0 %          |
| THM 6-2411WI |                                        | 5.0 VDC        | 1200 mA             | 86.0 %          |
| THM 6-2412WI |                                        | 12 VDC         | 500 mA              | 89.0 %          |
| THM 6-2413WI |                                        | 15 VDC         | 400 mA              | 89.0 %          |
| THM 6-2415WI |                                        | 24 VDC         | 250 mA              | 88.5 %          |
| THM 6-2421WI |                                        | ±5.0 VDC       | ±600 mA             | 85.0 %          |
| THM 6-2422WI |                                        | ±12 VDC        | ±250 mA             | 88.5 %          |
| THM 6-2423WI |                                        | ±15 VDC        | ±200 mA             | 88.0 %          |
| THM 6-4810WI | <b>18 – 75 VDC</b><br>(48 VDC nominal) | 3.3 VDC        | 1800 mA             | 82.5 %          |
| THM 6-4811WI |                                        | 5.0 VDC        | 1200 mA             | 86.5 %          |
| THM 6-4812WI |                                        | 12 VDC         | 500 mA              | 88.0 %          |
| THM 6-4813WI |                                        | 15 VDC         | 400 mA              | 88.5 %          |
| THM 6-4815WI |                                        | 24 VDC         | 250 mA              | 88.0 %          |
| THM 6-4821WI |                                        | ±5.0 VDC       | ±600 mA             | 85.0 %          |
| THM 6-4822WI |                                        | ±12 VDC        | ±250 mA             | 88.0 %          |
| THM 6-4823WI |                                        | ±15 VDC        | ±200 mA             | 88.0 %          |

## Input Specifications

|                                                                   |                                                                                                                                                                                                                    |
|-------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Input current at no load                                          | 5 Vin models: 20 mA typ.<br>24 Vin models: 6 mA typ.<br>48 Vin models: 4 mA typ.                                                                                                                                   |
| Start-up voltage / under voltage shut down                        | 5 Vin models: 4.5 VDC / 4.0 VDC typ.<br>24 Vin models: 9.0 VDC / 8.0 VDC typ.<br>48 Vin models: 18 VDC / 16 VDC typ.                                                                                               |
| Surge voltage (1 sec. max.)                                       | 5 Vin models: 16 VDC max.<br>24 Vin models: 50 VDC max.<br>48 Vin models: 100 VDC max.                                                                                                                             |
| Conducted noise                                                   | EN 55022 class A, without external components                                                                                                                                                                      |
| ESD (electrostatic discharge)                                     | EN 61000-4-2, air $\pm 8$ kV, contact $\pm 6$ kV, perf. criteria A                                                                                                                                                 |
| Radiated immunity                                                 | EN 61000-4-3, 10 V/m, perf. criteria A                                                                                                                                                                             |
| Fast transient / surge (with external input capacitor / diode)    | EN 61000-4-4, $\pm 2$ kV, perf. criteria A<br>EN 61000-4-5, $\pm 2$ kV perf. criteria A                                                                                                                            |
| – external input capacitor:                                       | 5 Vin models: Nippon chemi-con KY 1000 $\mu$ F/25 V and reverse diode (Vishay V10P45) in parallel<br>24 Vin models: Nippon chemi-con KY 470 $\mu$ F/ 50 V<br>48 Vin models: Nippon chemi-con KY 330 $\mu$ F/ 100 V |
| Conducted immunity                                                | EN 61000-4-6, 10 V, perf. criteria A                                                                                                                                                                               |
| External input fuse required (recommended values, slow blow type) | 5 Vin models: 5 A<br>24 Vin models: 2.5 A<br>48 Vin models: 1.5 A                                                                                                                                                  |

## Output Specifications

|                                           |                                                                                                                                                                                                                                                                                                                                                                                                          |
|-------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Voltage set accuracy                      | $\pm 1.0$ % max.                                                                                                                                                                                                                                                                                                                                                                                         |
| Regulation                                | – Input variation<br>single output models 0.2 % max.<br>dual output models 0.5 % max.<br>– Load variation 0 – 100 %:<br>single output models: 0.2 % max..<br>dual output models balanced load: 1.0 % max.<br>dual output models unbalanced load: 5.0 % max.                                                                                                                                              |
| Minimum load                              | not required                                                                                                                                                                                                                                                                                                                                                                                             |
| Start up time                             | 30 mS                                                                                                                                                                                                                                                                                                                                                                                                    |
| Ripple and noise (20 MHz Bandwidth)       | 3.3 & 5.0 VDC models: 30 mVp-p typ. with cap. 10 $\mu$ F/25V X7R MLCC<br>12 & 15 VDC models: 40 mVp-p typ. with cap. 10 $\mu$ F/25V X7R MLCC<br>24 VDC models: 50 mVp-p typ. with cap. 4.7 $\mu$ F/50V X7R MLCC                                                                                                                                                                                          |
| Transient response (25% load step change) | 250 $\mu$ s typ.                                                                                                                                                                                                                                                                                                                                                                                         |
| Current limitation                        | 150 % I <sub>out</sub> nominal typ. (hiccup mode)                                                                                                                                                                                                                                                                                                                                                        |
| Short circuit protection                  | continuous (automatic recovery)                                                                                                                                                                                                                                                                                                                                                                          |
| Over voltage protection                   | 3.3 VDC output models: 3.7 – 5.4 VDC<br>5 VDC output models: 5.6 – 7.0 VDC<br>12 VDC output models: 13.5 – 19.6 VDC<br>15 VDC output models: 18.3 – 22.0 VDC<br>24 VDC output models: 29.1 – 32.5 VDC                                                                                                                                                                                                    |
| Capacitive load                           | 3.3 VDC output models: 2100 $\mu$ F max.<br>5 VDC output models: 1500 $\mu$ F max.<br>12 VDC output models: 260 $\mu$ F max.<br>15 VDC output models: 210 $\mu$ F max.<br>24 VDC output models: 75 $\mu$ F max.<br>$\pm 5$ VDC output models: 860 $\mu$ F max. (each output)<br>$\pm 12$ VDC output models: 150 $\mu$ F max. (each output)<br>$\pm 15$ VDC output models: 100 $\mu$ F max. (each output) |

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.


## General Specifications

|                                                                       |                                                                                                    |                                                                                                                                                                 |
|-----------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Temperature ranges                                                    | <ul style="list-style-type: none"> <li>– Operating</li> <li>– Casing</li> <li>– Storage</li> </ul> | –40°C to +88°C (without derating)<br>+105°C max.<br>–55°C to +125°C                                                                                             |
| Humidity (non condensing)                                             |                                                                                                    | 95 % rel H max.                                                                                                                                                 |
| Temperature coefficient                                               |                                                                                                    | ±0.02 %/K typ.                                                                                                                                                  |
| Switching frequency                                                   |                                                                                                    | 250 kHz ±25 kHz. (puls width modulation)                                                                                                                        |
| I/O isolation voltage<br>(50Hz, 60sec.)                               | – to meet UL/IEC/EN 60601-1                                                                        | 5000 VACrms, rated for 250 Vrms working voltage, 2 x MOPP                                                                                                       |
| Clearance/creepage                                                    |                                                                                                    | 8 mm min.                                                                                                                                                       |
| Leakage current                                                       |                                                                                                    | 2 µA max. (at 240 VAC, 60 Hz)                                                                                                                                   |
| Isolation capacitance                                                 | – Input/Output                                                                                     | 17 pF max. (at 100 KHz, 1 V)                                                                                                                                    |
| Safety standards                                                      |                                                                                                    | ANSI/AAMI ES 60601-1:2005/(R)2012,<br>IEC/EN 60601-1 3rd edition                                                                                                |
| Safety approvals                                                      | – UL online certification UL 60601-1                                                               | <a href="http://www.ul.com">www.ul.com</a> File E188913, copy: e188913qqhm2.pdf                                                                                 |
| Reliability, calculated MTBF (MIL-HDBK-217F, at +25°C, ground benign) |                                                                                                    | >1.1 Mio. h                                                                                                                                                     |
| Casing material                                                       |                                                                                                    | non conductive plastic (UL 94V-0-rated)                                                                                                                         |
| Potting material                                                      |                                                                                                    | silicone (UL 94V-0-rated)                                                                                                                                       |
| Vibration and thermal shock resistance                                |                                                                                                    | according to MIL-STD-810F                                                                                                                                       |
| Weight                                                                |                                                                                                    | 14.0 g (0.48 oz)                                                                                                                                                |
| Soldering temperature                                                 |                                                                                                    | max. 265°C / 10 sec.                                                                                                                                            |
| Environmental compliance                                              | <ul style="list-style-type: none"> <li>– Reach</li> <li>– RoHS</li> </ul>                          | <a href="http://www.tracopower.com/products/reach-declaration.pdf">www.tracopower.com/products/reach-declaration.pdf</a><br>according RoHS directive 2011/65/EU |



- The component is not be used in an oxygen rich environment.
- The component is not to be used in conjunction with flammable anaesthetics and agents.
- The component has to be disposed appropriately. Please refer to local regulations (Waste Electrical and Electronic Equipment).
- A modification of the component is not allowed.

## Outline Dimensions



### Pin-Out

| Pin | Single     | Dual       |
|-----|------------|------------|
| 2   | –Vin (GND) | –Vin (GND) |
| 11  | No con.    | –Vout      |
| 14  | +Vout      | +Vout      |
| 16  | –Vout      | Common     |
| 22  | +Vin (Vcc) | +Vin (Vcc) |
| 23  | +Vin (Vcc) | +Vin (Vcc) |

Dimensions in [mm], ( ) = Inch  
 Pin diameter  $\varnothing 0.6 \pm 0.1$  ( $0.024 \pm 0.004$ )  
 Tolerances  $\pm 0.5$  ( $\pm 0.02$ )  
 Pin pitch tolerances  $\pm 0.25$  ( $\pm 0.01$ )

Specifications can be changed without notice! Make sure you are using the latest documentation, downloadable at [www.tracopower.com](http://www.tracopower.com)