





RELAY SOCKET ACCESSORIES

DIN RAIL

DRAWINGS & SPECIFICATIONS

PART NO.	DESCRIPTION	SERIES NO.
C-103-PM	Prepunched Aluminum DIN Rail (1 Meter Lengths) (note: Other lengths available, consult factory)	ES, GT, MT, OT, ST
	 Side view dimensions: 39.370 [1000.00] (total length), 1.083 [27.50] (top flange), 1.378 [35.00] (body), .177 [4.50] (bottom flange), .984 [25.00] (hole spacing), .709 [18.00] (bottom flange thickness). End view dimensions: .287 [7.29] (top flange), 1.378 [35.00] (body), .943 [23.95] (hole diameter), 1.063 [27.00] (bottom flange).	
C-104-PM	Prepunched Steel DIN Rail (1 Meter Lengths) (note: Other lengths available, consult factory)	ES, GT, MT, OT, ST
	 Side view dimensions: 39.370 [1000.00] (total length), .492 [12.50] (top flange), .984 [25.00] (hole spacing), .205 [5.20] (bottom flange), .709 [18.00] (bottom flange thickness). End view dimensions: .295 [7.50] (top flange), 1.378 [35.00] (body), 1.063 [27.00] (bottom flange).	
C-105-PM	Prepunched Steel DIN Rail (1 Meter Lengths) (note: Other lengths available, consult factory)	ES, GT, MT, OT, ST
	 Side view dimensions: 39.370 [1000.00] (total length), .492 [12.50] (top flange), .984 [25.00] (hole spacing), .248 [6.30] (bottom flange), .709 [18.00] (bottom flange thickness). End view dimensions: .039 [1.00] (top flange), .590 [15.00] (body), 1.378 [35.00] (body), 1.063 [27.00] (bottom flange).	
C-106-2PM	Prepunched Steel DIN Rail (2 Meter Lengths) (note: Other lengths available, consult factory)	ES, GT, MT, OT, ST
	 Side view dimensions: 78.740 [2000.00] (total length), .492 [12.50] (top flange), .984 [25.00] (hole spacing), .248 [6.30] (bottom flange), .709 [18.00] (bottom flange thickness). End view dimensions: .295 [7.50] (top flange), 1.378 [35.00] (body), 1.063 [27.00] (bottom flange).	

OTHER STYLES AND HOLE PATTERNS AVAILABLE. CONSULT FACTORY

25