


FILE NO.	BB-T-CD - 301 - 01
----------	--------------------

$$\begin{array}{r} .031 \\ 79 \overline{) 2.549} \end{array}$$
$$\begin{array}{r} .031 \\ .79 \overline{) 0.2549} \end{array}$$

$\frac{.081}{2.06}$ MIN.

$$\begin{array}{r} .165 \\ 4.19 \end{array}$$
$$\begin{array}{r} .165 \\ 4.19 \end{array}$$
$$\begin{array}{r} 650^{\circ} \text{ F} \\ 343^{\circ} \text{ C} \end{array}$$

WIRE SIZE: 16-14 AWG
1.0-2.5 MM²



PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES
BB-T-318-	$\frac{.534}{13.56}$	$\frac{.554}{14.07}$	$\frac{1.036}{26.31}$	10,14,56,38,413
BB-T-323-	$\frac{.250}{6.35}$	$\frac{.209}{5.31}$	$\frac{.560}{14.22}$	02,04,06,08
BB-T-325-	$\frac{.467}{11.86}$	$\frac{.388}{9.86}$	$\frac{.837}{21.26}$	10,14,56
BB-T-337-	$\frac{.312}{7.92}$	$\frac{.285}{7.24}$	$\frac{.645}{16.38}$	04,06,08,10 & 209
BB-T-339-	$\frac{.342}{8.69}$	$\frac{.310}{7.87}$	$\frac{.696}{17.68}$	04,06,08,10

DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		REFERENCE	SCALE:	NTS	DATE	TITLE:
FRAC.	DEC.	ANG.	DRWN. BY:	CHKD. BY:	APPRD. BY:	VERSAKRIMP 300-SERIES
±	±	±				



ETC
INCORPORATED

DWG. NO. **A** CUSTOMER DWG.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0148](#)