


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION . 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE APPROVED
✓	✓		D	REDRAWN-REVISED PER G-1479, G-1175, P85-0137 & P85-0138	2-13-86 pmm
✓	✓		E	OBSOLETE 1--4 PER G-2393	3-24-87 85 am
✓	✓		F	OBSOLETE 1--3 PER G-3358	4-22-88 m8 / 47
✓	✓		G	REV PER G-4732	JT 7-26-88 2.5
✓	✓		H	OBSOLETE 1--0 PER G-4184	JT 10-6-88 AGI
✓	✓		J	OBS. 1--2 PER G-4216	OKS 3-30-89 47
✓	✓		K	REV/0720-0066-93	4-14-93 T.Q./ml



- 1 WIRE INSULATION DIA: SEE TABLE.
2 TONGUE MATERIAL THK.: .031 ± .002

	.115-.170	100	LOOSE PC, BOX	8-328281-1
OBSOLETE	.115-.170	100	ON TAPE, SM. BOX	1-328281-4
OBSOLETE	.115-.170	1000	ON TAPE, LG. BOX	1-328281-3
OBSOLETE	.105-.170	5000	ON TAPE, REEL	1-328281-2
	.115-.170	5000	ON TAPE, REEL	1-328281-1
OBSOLETE	.105-.170	1000	LOOSE PIECE	1-328281-0
	.115-.170	—	LOOSE PIECE	328281

	WIRE INS. DIA.	QUANTITY	DESCRIPTION	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .008 ANGLES ± —				
MATERIAL INSULATION: NYLON - BLUE BODY & SLEEVE: COPPER (CQ-C-576) FINISH BODY & SLEEVE: TIN PL (MIL-T-10727) .000100 MIN. THK.				
CONTRACT NO. DR UTA/RFB 10-4-85				
CHK P. M. T. / 10-13-86 APPD C. M. T. / 10-13-86 APPD				
DSGN APPD OTHER APPD				
NAME AMP INCORPORATED Harrisburg, Pa. TERMINAL P.I.D.G., SPADE WIRE SIZE: 16-14				
SIZE B FSCM NO 00779 DRAWING NO 328281				
SCALE NTS SHEET 1 OF 1				