



Dimensions (In.)

Specifications:

- Type: 100 ft. spool IDC flat cable
- UL style: 2651
- UL flammability rating: VW-1
- Dielectric strength test: 2KV min. for 1 minute
- Conductor resistance: 237Ω/Km max.
- Insulation resistance: 100MΩ/Km min.
- Capacity: 40pF/m
- Impedance: 100Ω
- Voltage: 300V
- Temperature: 105°C
- Conductor: 28AWG 7/36 stranded, tin plated, copper wire
- Insulation: gray PVC

Mouser Stock No.	No. Cond.	Dim. (In.)	
		A	B
172-1402	14	.650	.700
172-1602	16	.750	.800
172-2002	20	.950	1.00
172-2402	24	1.15	1.20
172-2502	25	1.20	1.25
172-2602	26	1.25	1.30
172-3402	34	1.65	1.70
172-3602	36	1.75	1.80
172-5002	50	2.45	2.50
172-6402	64	3.15	3.20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[172-2402](#)