

■ Piezo Buzzer

Piezo Indicator(Internal Circuitry Type)

Pin Type

KPEG242


■ Shape

KPEG242




Rated Frequency (Hz)	4,100±500
Operating Voltage Range (V.D.C.)	3~16
Current Consumption (mA)	Max.7@12VDC
Sound Pressure Level (dB)	Min.70dB@30cm / 12VDC
Tone	Continuous
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Weight (Gram)	1.0
Material	Noryl(Black)

■ Dimension



Tol : ± 0.5 Unit : mm

■ Characteristic / Schematic Diagram



TOP 