




Passive - 2 wire  
8 Channel  
Input  
GE Fanuc






Passive - 2 wire  
8 Channel  
Output  
GE Fanuc



Passive - 2 wire  
8 Channel  
Output Fused w/MOV\*  
GE Fanuc



|                                                         |                                                         |                                                         |
|---------------------------------------------------------|---------------------------------------------------------|---------------------------------------------------------|
| RS PLC DI 8PT +/-                                       | RS PLC DO 8PT                                           | RS PLC DO W/F & MOV                                     |
| <b>998010</b>                                           | <b>998014</b>                                           | <b>996569</b>                                           |
| IC693MDL634                                             | IC693MDL730                                             | IC693MDL730                                             |
|                                                         | IC693MDL732                                             |                                                         |
|                                                         | <b>998015</b>                                           |                                                         |
|                                                         | IC693MDL731                                             |                                                         |
| 125 VDC                                                 | 12-24 VDC                                               | 12-24 VDC                                               |
| 3.0 A per channel / 6.0 A per module / 3.0 A per common | 3.0 A per channel / 6.0 A per module / 3.0 A per common | 2.0 A per channel / 6.0 A per module / 3.0 A per common |
| (1) 1 x 20 pin IDC                                      | (1) 1 x 20 pin IDC                                      | (1) 1 x 20 pin IDC                                      |
| No                                                      | No                                                      | No                                                      |
| 0°C...+50°C                                             | 0°C...+50°C                                             | 0°C...+50°C                                             |
| -20°C...+60°C                                           | -20°C...+60°C                                           | -20°C...+60°C                                           |
| 75 x 70 x 59                                            | 75 x 70 x 59                                            | 81 x 109 x 63                                           |
| #26...14 AWG                                            | #26...14 AWG                                            | #26...14 AWG                                            |
| Screw Clamp                                             | Screw Clamp                                             | Screw Clamp                                             |
|                                                         |                                                         |                                                         |



\*5 x 20 mm fuses required.  
Note: Markings vary based on I/O used.