

## For Patient-Care Areas - 4-outlet Medical-Grade Power Strip with cord wrap and drip shield

MODEL NUMBER: **PS410HGOEMX**



### Description

Tripp Lite's PS410HGOEMX Power Strip is designed to be installed on any mobile cart, diagnostic equipment, instrument, IV pole, etc. A built-in cord wrap system keeps unused cord organized securely in place, reducing tripping hazards and making the patient care area safer. The optional drip shield provides extra protection from liquids being used in the environment. It is TUV-tested to UL 1363A to supply power to plug-connected components of a movable equipment assembly that is rack, table or pedestal-mounted. It features 4 output receptacles, 10-ft. cord, and two built-in re-settable circuit breakers that control power to all outlets and protect against overloads. Switchless design prevents accidental shutoff. Optional-use keyhole mounting tabs and flanges.

### Features

More than a power strip, with the PS-410-HG-OEMX you get a built in cord management system and optional drip shield, providing extra protection. It's designed for use inside or outside the patient care area when mounted on any mobile cart, bed, IV pole, etc.

### Highlights

- Versatile power distribution strip designed to be installed on any mobile cart, bed, IV pole, etc.
- 10-ft. cord with integrated cord wrap system
- Optional drip shield included
- 4 hospital-grade receptacles and hospital-grade plug
- All metal housing with mounting ears / keyhole slots
- Tested to UL 1363A to supply power to plug-connected components of a movable equipment assembly that is rack-, table- or pedestal-mounted

### Applications

- Mobile carts, beds, IV poles and other UL 1363A certified usages.
- Can be used in Patient Care Areas, when properly mounted.

### Package Includes

- PS410HGOEMX Power Strip
- Owner's manual and warranty information

## Specifications

OVERVIEW	
Intended Application	Hospital/Medical
Style	Strip
Model Type	For Patient-Care Areas
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	15



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Outlet Quantity / Type	4 NEMA 5-15R-HG
Number of Outlets	8
Outlet Orientation	Single row of 4
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	No power switch
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	10.12 x 6.10 x 2.36
Shipping Dimensions (hwd / cm)	25.70 x 15.49 x 5.99
Shipping Weight (lbs.)	3.06
Shipping Weight (kg)	1.39
Unit Dimensions (hwd / in.)	9.94 x 4.28 x 2.17
Unit Dimensions (hwd / cm)	25.25 x 10.8712 x 5.51
Unit Weight (lbs.)	2.84
Unit Weight (kg)	1.29
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs and flanges enable mounting to a variety of surfaces
Receptacle Color	White
Color (AC Line Cord)	White
<b>CERTIFICATIONS</b>	
Approvals	TUV tested to UL 1363A
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.