


Dimensions: mm (in.)

**Electrical Specifications:**

- Contact Resistance: Max. 500mΩ (Initial)
- Dielectric Strength: 1,000VAC (50-60Hz) for one minute
1,000VAC (50-60Hz) for one minute
- Insulation Resistance: Min. 100 MΩ (At 100 VDC for 1 minute)
- Rating: 0.1A/12VDC

Note:

- RoHS Compliant

Mechanical Specifications:

- Operating Force (OF): Max. 90 gf
- Operating Angle: 10° ± 4°
- Maximum Angle: Max. 31°
- Operating Temperature: -40°C ~ 85°C
- Mechanical Life: Min. 100,000 cycles for each direct total 200,000 cycles
- Protection: IP67 with enclosure not include bare terminal

Snap Switch
101-35-5100-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-35-5100-EV](#)