

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		H	REV PER ECO-14-004548	26MAR2014	GG	JG

- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: HOUSING – POLYCARBONATE, CLEAR
TERMINAL – .36 [.014] THICK PHOSPHOR BRONZE PLATED WITH .178 μ m[.000007] THICK GOLD IN LOCALIZED PLATE AREA, OVER .762 μ m[.000030] THICK PALLADIUM NICKEL IN LOCALIZED PLATE AREA OVER 2.54 μ m[.000100] THICK NICKEL ON ENTIRE CONTACT.
SHIELD – COPPER ALLOY WITH 1.27 μ m[.000050] MINIMUM SEMI-BRIGHT (SATIN) NICKEL.
- 3

PLUG WILL ACCEPT 24 TO 28 AWG STRANDED WIRE, 0.74–0.99 [.029–.039] DIAMETER, WITH A 5.08 [.200] DIAMETER MAXIMUM JACKET.
- 4


TERMINATED DIMENSION 6.15 [.242] MAXIMUM.
- 5

500 ASSEMBLIES PER PACKAGE.
- 6

100 ASSEMBLIES PER PACKAGE.
- 8

SEE RESTRICTED CUSTOMER DRAWING 5-569532-5.
- 9

PACKAGED 10,000 ASSEMBLIES PER POLYBAG.



	8	5-569532-5
6	5	5-569532-3
9		5-569532-2
		5-569532-1
PACKAGED		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	25OCT2006	TE TE Connectivity		
		CHK	30OCT2006			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC		
MATERIAL		FINISH		APPLICATION SPEC		
2		2		108-1163		
				114-6016		
CUSTOMER DRAWING		WEIGHT		SIZE		
				A2 00779		
SCALE		SHEET		DRAWING NO		
4:1		1 OF 1		REV		
H		H		H		