



120mm sq.**San Ace 120****General Specifications**

- Material Frame: Plastics (Flammability: UL94V-0),
Impeller: Plastics (Flammability: UL94V-1)
- Expected Life Refer to specifications (L10:Survival rate:90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire ⊕red ⊖black (Sensor) yellow
- Storage Temperature -30°C to +70°C (Non-condensing)

120×120×25mm (Mass : 140g) **9S type** **Silent Fan****Specifications** The following nos. **have pulse sensors and ribs.** For ribless, append "1" to the model no.

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Airflow [m ³ /min] [CFM]	Max. Static Pressure [Pa] [inchH ₂ O]	SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]
9S1212H401	12	5.0 to 13.2	0.39	4.68	2,700	2.45 86.5	45.2 0.18	36	-10 to +60	40,000/60°C
9S1212F401		5.0 to 13.8	0.19	2.28	2,200	2.00 70.6	30.0 0.12	30		
9S1212M401		6.0 to 13.8	0.13	1.56	1,850	1.66 58.6	22.7 0.09	24		
9S1212L401		7.0 to 13.8	0.08	0.96	1,500	1.36 48.1	14.9 0.06	17		
9S1224M401	24	14 to 26.4	0.06	1.44	1,850	1.66 58.6	22.7 0.090	24		


Models without sensors, or with lock sensors, or PWM control function are available as options. Please refer to the index (p. 480).

Dimensions (unit: mm) (With ribs)**Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)**

Options (unit: mm)

Finger Guards


Model : 109-019C Surface treatment : Nickel-chrome plating (silver) Color
: 109-019H : Cation electropainting (black)



Mass : 32g

Resin Finger Guards


Model : 109-1000G



Mass : 23g

Model : 109-019E Surface treatment : Nickel-chrome plating (silver) Color
: 109-019K : Cation electropainting (black)


Inlet side, Outlet side



Mass : 42g


Resin Filter Kits

Model : 109-1000F13 (13PPI), 109-1000F20 (20PPI)
: 109-1000F30 (30PPI), 109-1000F40 (40PPI)




Mass : 44g


Airflow - Static Pressure Characteristics




9S1212H401




9S1212F401



9S1212M401



9S1212L401



9S1224M401

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sanyo Denki:

[9S1212P4M01](#) [9S1212P4M011](#) [9S1212M4021](#) [9S1212L402](#) [9S1212F402](#) [9S1212L4021](#) [9S1212F4021](#)
[9S1212M402](#) [9S1212P4F011](#) [9S1212P4F01](#) [9S1212F4D011](#) [9S1212H4D01](#) [9S1212H402](#) [9S1212F4D01](#)
[9S1212L4D011](#) [9S1212M4D011](#) [9S1212H4021](#) [9S1212M4D01](#) [9S1212P4H01](#) [9S1212P4H011](#) [9S1212L4D01](#)
[9S1224M402](#)