

		REVISIONS																																																																																
		REV	DESCRIPTION	DATE	APPROVED																																																																													
		042	UPDATED	8/1/94	BB																																																																													
.XXX = in XX.X = mm																																																																																		
<table><tr><th>ELECTRICAL</th><th>MECHANICAL</th><th>ENVIRONMENTAL</th></tr><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions MIL-STD-348A, Fig. 304.2</td><td>Temperature Rating -65°C to +125°C</td></tr><tr><td>Frequency Range (GHz) DC to 11</td><td>Recommended Mating</td><td>Vibration MIL-STD-202, Method 204, Condition B</td></tr><tr><td>Volt Rating (VRMS MAX) @ Sea Level 1000</td><td>Torque N/A</td><td>Shock MIL-STD-202, Method 213, Condition I</td></tr><tr><td>VSWR N/A</td><td>Mating Characteristics:</td><td>Thermal Shock MIL-STD-202, Method 107, Condition B, Except High Temp +115°C</td></tr><tr><td>Insertion Loss (dB MAX) N/A</td><td>Insertion (MAX lbs) 2.0</td><td>Moisture Resistance MIL-STD-202, Method 106</td></tr><tr><td>RF Leakage (dB MIN) N/A</td><td>Withdrawal (MIN oz) 2.0</td><td>Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray</td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) 500</td><td>Force to Engage and Disengage (in-lbs MAX) 3.0</td><td></td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 2500</td><td>Center Contact Captivation</td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX)</td><td>Axial (lbs) 6.0</td><td></td></tr><tr><td>Center Contact 1.0</td><td>Radial (in-oz) 4.0</td><td></td></tr><tr><td>Outer Contact .2</td><td></td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 1500</td><td></td><td></td></tr><tr><td>I.R.(Megohms MIN) 5000</td><td></td><td></td></tr></table>		ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 304.2	Temperature Rating -65°C to +125°C	Frequency Range (GHz) DC to 11	Recommended Mating	Vibration MIL-STD-202, Method 204, Condition B	Volt Rating (VRMS MAX) @ Sea Level 1000	Torque N/A	Shock MIL-STD-202, Method 213, Condition I	VSWR N/A	Mating Characteristics:	Thermal Shock MIL-STD-202, Method 107, Condition B, Except High Temp +115°C	Insertion Loss (dB MAX) N/A	Insertion (MAX lbs) 2.0	Moisture Resistance MIL-STD-202, Method 106	RF Leakage (dB MIN) N/A	Withdrawal (MIN oz) 2.0	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray	Corona, 70,000 Ft (VRMS MIN) 500	Force to Engage and Disengage (in-lbs MAX) 3.0		Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 2500	Center Contact Captivation		Contact Resistance (Milliohms MAX)	Axial (lbs) 6.0		Center Contact 1.0	Radial (in-oz) 4.0		Outer Contact .2			RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 1500			I.R.(Megohms MIN) 5000			<table><tr><td>HOUSING</td><td>STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303</td><td>NICKEL PLATE PER QQ-N-290</td></tr><tr><td>DIELECTRIC</td><td>TFE FLUOROCARBON PER ASTM-D-1457</td><td>N/A</td></tr><tr><td>CENTER CONTACT</td><td>BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>COMPONENT</td><td>MATERIAL</td><td>FINISH</td></tr></table>		HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	NICKEL PLATE PER QQ-N-290	DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A	CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204	COMPONENT	MATERIAL	FINISH	<table><tr><td rowspan="3">UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°</td><td>DRAWN BY ESC</td><td>DATE 11/30/70</td><td rowspan="3"></td><td rowspan="3">AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599</td></tr><tr><td>CHECKED BY PRS</td><td>12/2/70</td></tr><tr><td>APPD BY RPS</td><td>12/2/70</td></tr><tr><td rowspan="3">These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.</td><td colspan="2">USE ASS'Y PROCEDURE</td><td colspan="2">TITLE OSN FLANGE MOUNT JACK RECEPTACLE SOLDER POT TERMINAL</td></tr><tr><td colspan="2">NO. AP. N/A</td><td>SIZE B</td><td>CODE IDENT NO. 26805</td></tr><tr><td colspan="2"></td><td>SCALE 2:1</td><td>3052-0000-10</td></tr></table>		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	DRAWN BY ESC	DATE 11/30/70		AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	CHECKED BY PRS	12/2/70	APPD BY RPS	12/2/70	These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE		TITLE OSN FLANGE MOUNT JACK RECEPTACLE SOLDER POT TERMINAL		NO. AP. N/A		SIZE B	CODE IDENT NO. 26805			SCALE 2:1	3052-0000-10	REV 042
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																																																
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 304.2	Temperature Rating -65°C to +125°C																																																																																
Frequency Range (GHz) DC to 11	Recommended Mating	Vibration MIL-STD-202, Method 204, Condition B																																																																																
Volt Rating (VRMS MAX) @ Sea Level 1000	Torque N/A	Shock MIL-STD-202, Method 213, Condition I																																																																																
VSWR N/A	Mating Characteristics:	Thermal Shock MIL-STD-202, Method 107, Condition B, Except High Temp +115°C																																																																																
Insertion Loss (dB MAX) N/A	Insertion (MAX lbs) 2.0	Moisture Resistance MIL-STD-202, Method 106																																																																																
RF Leakage (dB MIN) N/A	Withdrawal (MIN oz) 2.0	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray																																																																																
Corona, 70,000 Ft (VRMS MIN) 500	Force to Engage and Disengage (in-lbs MAX) 3.0																																																																																	
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 2500	Center Contact Captivation																																																																																	
Contact Resistance (Milliohms MAX)	Axial (lbs) 6.0																																																																																	
Center Contact 1.0	Radial (in-oz) 4.0																																																																																	
Outer Contact .2																																																																																		
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 1500																																																																																		
I.R.(Megohms MIN) 5000																																																																																		
HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	NICKEL PLATE PER QQ-N-290																																																																																
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A																																																																																
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204																																																																																
COMPONENT	MATERIAL	FINISH																																																																																
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	DRAWN BY ESC	DATE 11/30/70		AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																																																														
	CHECKED BY PRS	12/2/70																																																																																
	APPD BY RPS	12/2/70																																																																																
These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE		TITLE OSN FLANGE MOUNT JACK RECEPTACLE SOLDER POT TERMINAL																																																																															
	NO. AP. N/A		SIZE B	CODE IDENT NO. 26805																																																																														
			SCALE 2:1	3052-0000-10																																																																														
		SHEET 1 OF 1																																																																																