




AD6015(T)-7 SERIES

External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Lead wire:UL1007AWG26

Specifications(Nominal)


*:Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow		Maximum Pressure		*Noise Level (dB/A)	Weight (g)
							(CMM)	(CFM)	(InAq)	(mmAq)		
60x60x15	AD0605LB-D70GL(T)	◎ ※ ●	5	0.10	0.50	3500	0.348	12.332	0.081	2.057	24.8	38.0
	AD0605MB-D70GL(T)	◎ ※ ●	5	0.18	0.90	3900	0.405	14.324	0.122	3.098	28.8	
	AD0605HB-D70GL(T)	◎ ※ ●	5	0.19	0.95	4500	0.447	15.816	0.146	3.708	33.4	
	AD0612DB-D70GL(T)	◎ ※ ●	12	0.06	0.72	3100	0.305	10.801	0.064	1.625	21.3	
	AD0612LB-D70GL(T)	◎ ※ ●	12	0.07	0.84	3500	0.348	12.332	0.081	2.057	24.8	
	AD0612MB-D70GL(T)	◎ ※ ●	12	0.08	0.96	3900	0.405	14.324	0.122	3.098	28.8	
	AD0612HB-D70GL(T)	◎ ※ ●	12	0.09	1.08	4500	0.447	15.816	0.146	3.708	33.4	
	AD0612UB-D70GL(T)	◎ ※ ●	12	0.12	1.44	5100	0.519	18.361	0.169	4.292	38.6	
	AD0624LB-D70GL(T)	◎ ※ ●	24	0.03	0.72	3500	0.348	12.332	0.081	2.057	24.8	
	AD0624MB-D70GL(T)	◎ ※ ●	24	0.04	0.96	3900	0.405	14.324	0.122	3.098	28.8	
	AD0624HB-D70GL(T)	◎ ※ ●	24	0.05	1.20	4500	0.447	15.816	0.146	3.708	33.4	
	AD0624UB-D70GL(T)	◎ ※ ●	24	0.06	1.44	5100	0.519	18.361	0.169	4.292	38.6	

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以2Ball為主, 若需其他產品資訊請聯絡您在ADDA的業務代表, 謝謝!!)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓					✓					

*Safety approvals

UL	UL	SP	CE	CE
✓	✓		✓	✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AD0605HB-D73GL-LF](#) [AD0612HB-D76GL-LF](#) [AD0612DX-D70GL-LF](#) [AD0612MB-D71GL-LF](#) [AD0624HB-D71GL-LF](#)
[AD0612MB-D76GL-LF](#) [AD0612DB-D70GL-LF](#) [AD0612DB-D70GL\(T\)-LF](#) [AD0624HX-D71GL-LF](#)