


2997 \pm 76
 — PLUG TYPE:
 NEMA 5-15P
 — CONNECTOR TYPE:
 IEC 60320 C-13
 — BROWN
 — BLUE
 — GREEN/YELLOW

VOLEX RESERVES THE RIGHT TO
 ALTER NON-CRITICAL DIMENSIONS
 WITHOUT NOTICE.

PACKAGING: FOLD & TIE



229 \pm 76

NOTES

- 1) CORDAGE: CORDAGE: 14/3 SJT, FOIL SHIELDED WITH DRAIN WIRE, 60°C, BLACK
- 2) APPROVALS: 
- 3) RATING 15 AMP/125 VOLTS
- 4) FLAME RATING : FT2
- 5) DRAIN WIRE CONNECTED TO GROUND PIN OF PLUG MOLD ONLY. DRAIN WIRE IS CUT FLUSH WITH JACKET EDGE PRIOR TO MOLDING CONNECTOR.
- 6) ALL DIMENSIONS IN MILLIMETERS.
- 7) PACKAGING: 50 PIECES/CARTON.

REV

1 C.U.D - NEW RELEASE

7/26/07

DESCRIPTION


DATE

MATERIAL:
 PLUG: PVC, BLACK
 JACKET: PVC, BLACK
 RoHS/Prop 65 Compliant

SCALE:
 NUT TO
 SCALE

EC0:
 N/A

ITEM
 DESCRIPTION:
 SHIELDED CORDSET-NORTH AMERICAN
 DETACHABLE POWER SUPPLY CORD(9'10")



FORM IN71-07 REV A

Indianapolis, IN
 Conover, N.C.
 Fremont, CA
 Aguascalientes, MX
 Tijuana, Mexico
 Hermosillo, MX
 Clinton, AR
 Kanata, Canada

This document is the property
 of Volex Incorporated. The
 information contained herein is
 not to be disclosed to anyone
 without the express written
 consent of Volex Inc.

17605 10 B1