

WCY58

WCY58

WCY58 : WEJTAP CONN YEL



ACTIVE

RoHS compatible

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Specifications

Download document

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Conductor Size (Run - Diameter)	0.666 to 0.893		
Conductor size (Run - Max)	5565		
Conductor size (Run - Min)	397.5-18/1		
Conductor Size (Run - mm)	17 mm² to 23 mm²		
Conductor Size (Run)	556.5		
	397.5-18/1		
	477		
	477.0-18/1		
Conductor size (Tap - Max)	#4-6/1		
Conductor size (Tap - Min)	#4		
Conductor Size (Tap)	#4-6/1		
	#4		
Conductor Type (Run)	ACSR		
	AAC		
Wire Size	AWG		
Wire Size (Tap - Diameter - in)	0.204 to 0.258		
Wire Size (Tap - mm)	5 mm² to 7 mm²		
Wire Type (Tap)	ACSR		
	AAC		
	Copper		
Physical			
Color Code	Yellow		
Approvals / Certifications			
UL Listed	No		
CSA Certified	No		
Other Features			
Installation Tool	WTRB		
Booster	WPBY Box 25		
UPC	78181087430		
Keyword	wejtap		