












- NOTES:
1. USE #4 TYPE "B" THREAD FORMING SCREWS X .25 [6.3] LONG.
 2. RECOMMENED ASSEMBLY SCREW TORQUE SETTING IS 5 INCH-POUNDS.
 3. TO MAINTAIN IP67 RATING USE THE GASKET ONCE; IF OPENING UNIT TO SERVICE MUST REPLACE GASKET.

PCB LOCATION	DIMENSION			
	H	J	K	L
TOP COVER	.369 [9,38]	2.669 [67,8]	.719 [18,27]	4.819 [122,41]
BOTTOM COVER	.344 [8,74]	2.694 [68,43]	.744 [18,7]	4.794 [121,77]

PACNTEC®
1-610-361-4231

OD36-2.0

VISIT **PACNTEC®**
ON THE WORLD WIDE WEB
www.pactecenclosures.com

SCALE: .9

MATERIAL:
POLYCARBONATE (HB)
WITH UV STABILIZER

COLOR:
LIGHT GRAY #332

INSERT AREAS ARE SECTIONS IN OUR TOOLS
THAT CAN BE REMOVED AND REPLACED WITH
CUSTOMER SPECIFIC DETAILS

DRAWING NUMBER	REV
83748	D